

1U 4-Post Adjustable Vented Server Rack Mount Shelf - 330lbs(150 kg) - 19.5 to 38in Adjustable Mounting Depth Universal Tray for 19" AV/ Network Equipment Rack - 27.5in Deep

**Product ID:** ADJSHELFHDV



The ADJSHELFHDV 1U 4-Post Adjustable Heavy Duty Vented Rack Mount Shelf lets you add a high-capacity, adjustable 1U shelf to virtually any standard 19-inch 4-post server rack or cabinet.

This heavy duty rackmount shelf can be adjusted from 19.5in to 38in (mounting depth) to fit your rack, while the vented design improves air flow and help to lower temperatures in the rack. Constructed using 1.2mm SPCC commercial grade cold-rolled steel, providing the ability to hold up to 150kg (330lbs) of equipment - a durable solution for storing large, non-rackmount pieces of equipment, heavy tools or peripherals in your rack or cabinet.

The ADJSHELFHDV is backed for life, including free lifetime 24/5 multi-lingual technical assistance.

## Certifications, Reports and Compatibility



## Applications

- Adding a storage shelf to shallow depth network switches/equipment racks
- Supply additional storage space for heavy, mission critical hardware and non-rack mount equipment
- For use with all 19" wide Server Racks and Cabinets

## Features

- **UNIVERSAL 19" FIT:** This vented server rack mount shelf works with 19in 4-post server racks and has a fixed surface depth of 27.56in, and an adjustable mounting depth range of 19.5-38in for your data, networking or other small-form tools / equipment
- **COMPACT DESIGN:** The adjustable vented rack shelf features a very compact form factor, making it ideal for non-rackmount equipment, tools and peripherals in your home, studio or office space
- **HEAVY-DUTY & DURABLE DESIGN:** Constructed with SPCC commercial cold-rolled steel, the sturdy IT-grade cabinet shelf ensures long term durability and supports a total weight load of 330 lb / 150 kg
- **VERSATILE FUNCTIONALITY:** With a surface depth of 27.56in and adjustable mounting depth range of 19.5-38in, this shelf can work with any 19 inch 4-post cabinet or equipment rack - It provides additional storage space for your tools or A/V accessories
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this adjustable vented rack shelf is backed for life, including free lifetime 24/5 multi-lingual technical assistance

#### Hardware

|                    |                              |
|--------------------|------------------------------|
| Warranty           | Lifetime                     |
| Frame Type         | Steel                        |
| U Height           | 1U                           |
| Cable Management   | No                           |
| Industry Standards | EIA RS310-D                  |
| Mounting Options   | Front Mount (Front and Rear) |

#### Performance

|                              |                                                                                        |
|------------------------------|----------------------------------------------------------------------------------------|
| Weight Capacity (Stationary) | 330.8 lb [150 kg]                                                                      |
| General Specifications       | Weight Capacity: Rev 01 - up to 250lbs / 113kg; Rev 02 or above - up to 330lbs / 150kg |

#### Physical Characteristics

|                |                   |
|----------------|-------------------|
| Color          | Black             |
| Material       | Steel             |
| Rail Thickness | 0.0 in [1.2 mm]   |
| Product Length | 27.6 in [70.0 cm] |
| Product Width  | 17.6 in [44.6 cm] |

|                        |                   |
|------------------------|-------------------|
| Product Height         | 1.8 in [4.5 cm]   |
| Weight of Product      | 12.5 lb [5.6 kg]  |
| Maximum Mounting Depth | 38.3 in [97.4 cm] |
| Minimum Mounting Depth | 19.5 in [49.5 cm] |

---

#### Packaging Information

|                           |                   |
|---------------------------|-------------------|
| Package Quantity          | 1                 |
| Package Length            | 21.7 in [55.2 cm] |
| Package Width             | 30.1 in [76.4 cm] |
| Package Height            | 4.6 in [11.8 cm]  |
| Shipping (Package) Weight | 15.0 lb [6.8 kg]  |

---

#### What's in the Box

|                     |                                       |
|---------------------|---------------------------------------|
| Included in Package | 1 - 1U High Cap Adjustable Rack Shelf |
|                     | 1 - Instruction Manual                |
|                     | 1 - 1U Shelf Body                     |
|                     | 2 - Front Mounting Brackets           |
|                     | 2 - Rear Mounting Brackets            |
|                     | 8 - M6x12mm Mounting Bracket Screws   |
|                     | 8 - M6x12 mm Screws                   |
|                     | 8 - M6 Cage Nuts                      |
|                     | 8 - M6 Plastic Washer                 |
|                     | 1 - Quick-start Guide                 |

---

***\*Product appearance and specifications are subject to change without notice.***