



ENGLISH

Datasheet  
**Stock No. 811-2233**  
**Local Air Conditioner**



**Specifications:**

Power Supply	220-240V~, 50Hz
Cooling Capacity	12000 BTU / 3.5KW
Power/Ampere Consumption For Cooling	1300W / 5.9A
Air Volume (max.)	480 m3/h
Working Temperature	18 ~ 32oC
Fan Speed	3
Timer	1~24 hours
Sleep Function	Yes
Water Tank	3.5 L
Refrigerant	R410A

Exhaust Pipe	Dia. 142 x 1.5 M (max.)
Net Weight	29.5 kg
Product Size (WxDxH)	420 x 405 x 790 mm
Test condition	DB 35°C, WB

#### Features:

With EER certificate --- A

3 working mode: Auto, Cool, Fan

3 fan speed: High, Medium, Low

Easy installation with exhaust pipe and PVC window kit

Concealed caster, convenient for moving about and storage

Washable dust filter plus active carbon filter

Pre-set timer available

Continuous drainage available

