

# Deck lights extension kit warm white and RGB



## PRODUCT DATA

Power:	Max 0.7 W
Lumen:	50 lm
Color:	RGB and warm white
White temperature:	2700K
Dimensions:	IP54
Operating temperature:	-20°C to 45°C
Wi-Fi Frequency:	2.4 GHz
Network protocol:	IEEE 802.11 b/g/n
Power (one light):	Max 0.7 W
Lumen (one light) :	50 lm
Color:	RGB and warm white
White temperature:	2700K
Dimensions:	H26 x Ø45 mm
Drilling hole:	Ø32 mm
Cable length:	2x 50 cm
Space between lights:	Up to 1 m
Functions:	Dimmer, timer, remote control, color control
Ingress protection:	IP54
Operating temperature:	-20°C to +45°C
Compatibility:	This product requires SH-DLK01
Package contents:	5x lights, 1x 2m extension cable, protection cap and manual.

## LOGISTICS DATA

Article number:	SH-DLEX01
Brand:	DELTACO
EAN code:	7333048052216
Country of origin:	China
Custom tariff number:	9405409000
Master carton packing unit:	30 pcs
Master carton gross weight:	14.6 kg
Master carton dimensions:	45.3 x 27.8 x 32.7 mm
Package type:	Box
Package weight:	406 g
Package dimensions:	155 x 50 x 145 mm
Article weight:	406

**Wi-Fi  
Dimmer  
0.7W/50lm  
Amazon Alexa & Google Home**

