this is proformance



ID 1/4" 18.0-EC HD/5.0

Set

Cordless impact wrench 18,0 V with bit ejector Order no. 520771
GTIN 4030293239654

- Brushless motor with greater efficiency and a longer service life
- Electronic management system (EMS) protects the machine, extends the service life, and increases efficiency
- Tap mode for self-tapping short and long screws. Screw overtightening or breakage is prevented
- With bit ejector for quick and easy bit change
- The short head length makes it ideal for screwdriving in confined areas
- Extremely high speed and torque enable efficient work
- Speed Command: three different speed settings for a variety of applications. Prevents, among others, over tightening of small screws
- 1/4" hex tool holder
- Electronic quick-acting brake
- Right/left rotation with safety catch
- Robust gearbox housing made of die-cast aluminium with protective cap
- c Ergonomically designed, non-slip, soft grip handle
- Integrated LED lamp with persistence function
- LED battery capacity display
- Including belt clip and bit storage
- FLEX battery system: suitable for all FLEX 18 V battery packs









Technical data

Battery voltage	18.0 V
Battery capacity	2.5 / 5.0 / 8.0 Ah
Torque settings	3 Steps
Max. torque, setting 1	58 Nm
Max. torque, setting 2	104 Nm
Max. torque, setting 3	237 Nm
No-load speed	3700 rpm
Tool holder, impact drill	1/4" inside
Dimensions WxLxH	119 x 76 x 208 mm
Weight without battery pack	1.2 kg

Standard equipment

- 1 Bit storage
- 1 Belt clip
- 1 Rapid charger (417882)
- 1 Carrying case L-BOXX® (414085)
- 1 Case insert
- 2 Li-Ion rechargeable battery pack 18,0 V (532733)