

Polyurethane recoils with prevoS1 safety release quick couplers



Technical characteristics

Max operating pressure: 8 bar

Temperature: -15°C to +70°C

Construction: Polyurethane

Highlight: Excellent shape memory

Equipped with: Swivel fitting

ID/OD (mm)	Profile	Coupler	Max length (m)	Parts Numbers
5 x 8	European 7.4 mm	ESI 07	2	PUS 52ES
5 x 8	European 7.4 mm	ESI 07	4	PUS 54ES
6.5 x 10	European 7.4 mm	ESI 07	4	PUS 64ES
6.5 x 10	European 7.4 mm	ESI 07	6	PUS 66ES
6.5 x 10	European 7.4 mm	ESI 07	8	PUS 68ES
8 x 12	European 7.4 mm	ESI 07	4	PUS 84ES
8 x 12	European 7.4 mm	ESI 07	6	PUS 86ES
8 x 12	European 7.4 mm	ESI 07	8	PUS 88ES