

Wire Size Capacity (Maximum), EN 60204-1, Stranded Cu	12 / 14 (2) AWG, 4 / 2.5 (2) mm ₂
DIN Rail Mounting, EN 60715	35 mm
Chassis Mount Screw Torque	7 / 0.8 Lb-in / Nm
Flammability Rating	94V-0 Class
Body Color	Light Gray
DIN Locking Method	Metal Compression Spring

Product Certifications

Agency Approvals	CE RoHS UL CSA
-------------------------	-------------------------