

NPR-3300-RT
NETYS PR RT 3300VA RK/TW

The NETYS PR is the ideal solution for protecting small servers, networking devices and peripherals.


Strong points

- A secure and professional supply continuity
- Tailored to IT networking
- Simple to install
- Protection for your data line
- Meets practical needs
- Easy to use and to integrate

General characteristics

- 19" Rack & Rack/Tower convertible UPS.
- Sine Wave, AVR function (Automatic Voltage Regulation).
- Clear and uncluttered LCD interface.
- Wide range of communication protocols available in options.
- NTP data line suppressor.
- Up to 9 UPS output sockets.

Compliance with standards

- IEC/EN 62040-1, IEC/EN 62040-2
- AS 62040.1.1, AS 62040.1.2, AS 62040.2
- CE
- RCM (E2376)

Access to resources (ex: manuals)
Technical Characteristics

Length of the product unit [mm]	87
Width of the product unit [mm]	440
Depth of the product unit [mm]	608
Weight [kg]	31.5
Depth [mm]	608
Height [mm]	87
In/out	1/1
Output voltage	230
Rated frequency	50/50
Width [mm]	440
Sn [kVA]	3.3
Pn [kW]	2.7
Conf	M2
Input voltage	230
Rate (min)	3.3
Rate (max)	3.3
Life Time	03-05
Typical Backup Time [min]	8
Configuration	Line-Interactive UPS with AVR

Classification

UNSPSC	39121011
ETIM Class	EC000382
IGCC	4149

Commerce

Description	NeTYS PR-RT 3300VA/2700W 230V 50/60Hz WITH AVR, SINEWAVE,LCD PLUGSPROTECTEDRJ45,1xUSB,1xRS232 BATTERY INCLUDED
Effective date	2012-09-01
Offer Life Cycle Code	40
Country of origin	CN

ETIM - Electrical characteristics

Input voltage [V]	161..276
Primary frequency [Hz]	45..66
Number of phases primary	1
Output voltage [V]	230..230
Secondary frequency [Hz]	50..60
Output effective power [W]	2700
Output apparent power [VA]	3300
Number of phases secondary	1
SNMP	Yes
Voltage type	AC
Output power factor	0.8

ETIM - Mechanical characteristics

Height [mm]	87
-------------	----

Width [mm]	440
Depth [mm]	608
Weight [kg]	31.5
Construction type	Free standing model
Input connection	C20
Number of output connections C13	8
Number of output connections C19	1
ETIM - Technical features	
USB interface	No
Bridging time full load [min]	8.5
Suitable for network-management	Yes
USV- technology	Line-interactive
Overall efficiency [%]	98
Efficiency in eco-mode [%]	98
Potential free switch contact	Yes
Auto shut down function	Yes
Logistics	
GTIN/EAN	8027122515344
Customs number	8504409590
Weight of the packing unit [kg]	31.5
Length of the packing unit [m]	0.608
Width of the packing unit [m]	0.44
Depth of the packing unit [m]	0.087
Norms	
Conformity to standards	IEC