

3-970  **BERNSTEIN** TECHNICline Set of pliers

4-piece set dissipative pliers from the series TECHNICline in cases made from dissipative black imitation leather, with zip fastener

No.	Description of individual tools	Weight: 0.400 kg
3-963-15	Mini side cutters TECHNICline, 120 mm, ultra flush, for soft wire up to 1.3 mm Ø, medium hard wire up to 0.7 mm Ø, precision joint with screw system, double leaf spring, non-reflective surface, dissipative bicoloured hand guard	
3-971-15	Side cutters TECHNICline, 125 mm, semi flush, for soft wire up to 1.6 mm Ø, medium hard wire up to 1.0 mm Ø, hard wire up to 0.5 mm Ø, precision joint with screw system, double leaf spring, non-reflective surface, dissipative bicoloured hand guard	
3-992-15	Flat nose pliers TECHNICline, 130 mm, short plain jaws, finish as above	
3-683-15	Spitzzange TECHNICline, 140 mm, long plain jaws, finish as above	



3-970

## SIDE CUTTERS, TELEPHONE AND COMBINATION PLIERS

lap joint, bright polished – chrome–plated with dissipative black hand guard

No.	Length mm	Head- width mm	Finish	Cutting capacity		Weight g
				Wire soft	mm Ø hard	

### Side cutters

swedish design

3-133-13	145	19	special steel	2.5	1.25	155
----------	-----	----	---------------	-----	------	-----

### Telephone pliers

snipe nose, long straight jaws, with cutting edges for hard wire

3-245-13	200	18.5	serrated jaws			180
----------	-----	------	---------------	--	--	-----

### Combination pliers

with wire cutter, for hard wire

3-732-13	165	23	serrated jaws			185
----------	-----	----	---------------	--	--	-----



3-133-13



3-245-13



3-732-13