

4690

COVERALL

SIZES:

S-4XL Reg leg (31"/80cm)
M-2XL Tall leg (33"/85cm)

Internal elasticated
waistband for
improved fit



Wear with
kneepads for
extra protection



Double
stitched
5cm FR AS
reflective
tape

IMPROVED

4692

LADIES COVERALL

SIZES:

8-16 Reg leg (29"/75cm)



Cut in a
specific
women's fit

- ✓ Mandarin collar // Maximum neck protection
- ✓ Kneepad pockets // Wear with kneepads for extra protection
- ✓ Chest pockets with flaps // Secure storage
- ✓ Gas monitor loop // Secure fixing point
- ✓ SafetyICON™ on arm // Visual EN Standard
- ✓ 5cm FR AS reflective tape // Double stitched for longer life
- ✓ Phone pocket on sleeve with flap // Safe and secure
- ✓ Velcro® secured cuff tabs // Close fit around wrist or gloves
- ✓ Side access pockets // With entry inside coverall
- ✓ ThermSAFE™ plastic FR zippers // CE Certified
- ✓ Internal elastic 2 point adjustable waistband // Ensures close fit
- ✓ Triple stitched side seams // Lifetime quality assurance
- ✓ Easy-Stretch™ side panels // Maximum wear comfort

PRODUCT INFORMATION

COLOUR: HV Orange

FABRIC SPECIFICATION:
ProGARM® VXS+ Inherent Woven
Fabric, HV Orange - 290gms

PRODUCT CARE:



EN STANDARDS

EN ISO 11612: 2015	EN 1149-5: 2018	EN 61482-2: 2020	EN ISO 11611: 2015	EN ISO 20471: 2013 + A1:2016	Compliant
A1, B1, C1, F1	Pl. 5:2018 Pl. 3:2004 Charge Decay	APC1 ATPV=9.3cal/cm² ELIM=8cal/cm²	Class 1, A1	Class 3	Issue 2

BOX TEST



ARC RATING



FABRIC

