

## M18 CCS55-502X | M18 FUEL™ 55mm circular saw for wood and plastics

Article: 4933451377



- Milwaukee® designed and built brushless POWERSTATE™ motor for up to 3x longer motor life and up to 2x more cuts per charge.
- Integrated battery fuel gauge & LED light.
- Flexible battery system: works with all Milwaukee® M18™ batteries.
- REDLINK PLUS™ intelligence system delivers an advanced digital overload protection for tool and battery and uniquely enhances the tool performance under load.
- REDLITHIUM-ION™ battery pack provides superior pack construction, electronics and fade-free performance to deliver more run time and more work over pack life.
- Individual battery cell monitoring optimises tool run time and ensures long term pack durability.
- 50° bevel capacity.

M18 CCS55-502X	
Sound pressure level (dB(A))	80.8
Sound pressure level uncertainty (dB(A))	3
Sound power level (dB(A))	91.8
Sound power level uncertainty (dB(A))	3
Vibration level (m/s <sup>2</sup> )	2.45
Vibration uncertainty (m/s <sup>2</sup> )	1.5
Bore size (mm)	15.87
No load speed (rpm)	5000
Voltage (V)	18
Battery pack capacity (Ah)	5.0
Battery type	Li-ion
Supplied in	HD Box
Charger supplied	59 min
No. of batteries supplied	2
Blade diameter (mm)	165
Article Number	4933451377
Weight with battery pack (kg)	3.2
Max. cutting depth 45° (mm)	41
Max. cutting depth 90° (mm)	55