

Datasheet

Stock No: 178-5733

RS Pro Thermal Line Panel Printer Ultra High Speed



Specification	
Print Method	Thermal Line
Print Speed	170 mm/s
Resolution	8 dots/mm, 576 dots/line
Effective Printing Width	72mm
Character Set	ASCII, GB18030(Chinese), BIG5
Print Font	Codepage, ANK:12×24; Chinese: 24×24
Paper Type	Thermal Paper
Paper Width	79.5± 0.5mm
Paper Thickness	0.06~0.08mm
Paper Roll Diameter	Max: 80.0mm
Roll Core Inner Diameter	13mm(min.)
MCBF Reliability	1million lines
Barcode	1D: UPC-A, UPC-E, EAN-13, EAN-8, CODE39, ITF25, CODEBAR, CODE93, CODE 128 2D: PDF417, QRCODE, DATAMATRIX
Emulation	ESC/POS
Driver	Windows98/2000/NT/XP/Vista/Win7/Win8
Interface	RS-232 + USB
Paper Supply Method	Drop-in easy paper loading
Power Supply (Adapter)	DC 24V, 2A
Outline Dimension (WxDxH)	132x125.5x89mm
Installation Port Size	122x128x86.7mm
Weight	400g
Operating Temp	0 ~ 50 °C

Operating Humidity

20 ~ 80%

**ENGLISH**