

PRODUCT-DETAILS

TC5350A-TB

LATCHG CLAMP .98X.98IN NAT SCR/AD



General Information

Extended Product Type	TC5350A-TB
Product ID	7TCG009890R0002
EAN	5414363059042
Catalog Description	LATCHG CLAMP .98X.98IN NAT SCR/AD
Long Description	Re-Usable Latching Cable Clamp, Natural Nylon 6.6 for Temperatures up to 85 Degrees Celsius (185 F), Length of 25.0mm (0.984 Inches), Width of 25.0mm (0.984 Inches), Maximum Height of 22.0mm (0.87 Inches), Self-Adhesive or Screw Mounting Method, Mounting Hole Diameter of 4.3mm (0.17 Inches), 100 Pack

Ordering

EAN	5414363059042
UPC	786210804927

Dimensions

Product Net Weight	.006 lb 2.721 g
--------------------	--------------------

Container Information

Package Level 1 Units	100 piece
Package Level 2 Units	1000 piece

Package Level 2 Width	15.4 in 391 mm
Package Level 2 Height	11 in 279 mm
Package Level 2 Depth / Length	23.6 in 599 mm

Additional Information

Brand / Label	Ty-Rap
Color	Natural
Material	Nylon/Polyamide 6.6
Mounting Type	Screw
Number of Batteries	0
Process Temperature Rating	-40 to +185 °F
Product Name	CABLE TIE NYLON MOUNTING CLAMP
Product Type	One-Piece Mounting Clamp
Special Functions	Integral top cover incorporates a unique ratchet design that is fully adjustable and releasable.

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TC5350A-TB
Instructions and Manuals	TC5350A-TB

Classifications

ETIM 6	EC000449 - Mounting base and -element for cable ties
ETIM 7	EC000449 - Mounting base and -element for cable ties
UNSPSC	39121717
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5065 >> Cable tie mounts

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

