



POLIFAN POWER flap disc PFF 125x22.23 mm flat Z40 SG POWER STEELOX steel/stainless steel

**POLIFAN POWER flap disc PFF 125x22.23 mm flat Z40 SG
POWER STEELOX steel/stainless steel**

Item number: [67684125](#)

EAN: [4007220167625](#)

The broad range Performance Line SG offers a high-performance tool solution for every application and every material. Performance Line SG tools achieve optimum results with maximum economic efficiency.

The POLIFAN POWER flap disc stands out due to its aggressive stock removal rate and excellent tool life while achieving maximum economic efficiency. It is the best conventional flap disc for steel.

For discerning users, the high-performance POLIFAN POWER flap disc is the first choice worldwide for the machining of steel. The versatile POLIFAN flap disc offers an optimal combination of excellent tool life and maximum stock removal rate.

Technical information

Abrasive	Zirconia alumina Z
Dia. external	125 mm
Dia. hole	22.23 mm
Grit size	40
Max. RPM	12200 RPM
Mounting system	Centre hole
Shape	PFF / A / T27
Version	No information

Advantages

- ✓ Fast work progress and maximum economic efficiency thanks to the aggressive stock removal rate.
- ✓ Maximum aggressiveness over the entire tool life.
- ✓ Fewer tool changes due to the excellent tool life.

Recommendations for use

- ✓ Also suitable for surface grinding on steel.

Materials that can be worked

- ✓ Stainless steel (INOX)
- ✓ Steel

Applications

- ✓ Chamfering
- ✓ Deburring
- ✓ Work on weld seams

Drive types

- ✓ Angle grinder
 - ✓ Drive spindle
-



August Rüggeberg GmbH & Co. KG
Hauptstraße 13
51709 Marienheide

+49 2264 9-0

+49 2264 9-400

info@pferd.com