

2150 10

3C-Screwdriver

for slotted head screws

Code	ETIM
6679860	EC000158
EAN	UNSPSC
4010886806661	27-11-17-01
Country of origin	eCl@ss
Slovenia	21-04-04-01
Customs tariff number	
82054000	



Article description

- Acc. to DIN ISO 2380-2, cutting edge according to DIN ISO 2380-1 Form A
- 3-component handles Power-Grip³ with hanging hole
- Ergonomic handle shape for accurate, non-tiring work
- Positive connection of handle and blade for optimum power transmission
- Type of drive marked at the end of the handle
- Blade of galvanised molybdenum-vanadium steel

Article information

Contents (Qty of pieces)	1	Cap rotatable	no
Version/Execution	with hanging hole	Anti-magnetic	no
Net weight [kg]	0,203 kg	Ball head	no
Total length [mm]	320 mm	Handle available	yes
Material	Molybdenum-vanadium-steel	Isolated	no
Blade length	200 mm	Corrosion Protected	no
Standard	DIN ISO 2380-2	Colour coding	no
Blade width [mm]	10,0 mm	Unit-tested	no
Low sparking design	no	Handle design	3C
Blade shape	Round	Output tip reference standard	DIN ISO 2380-1 - Form A
Blade diameter	8,0 mm	Drive hexagon	no
Roll protection	no	Blade thickness	1,6 mm
Impact cap	no		