

# Specifications

## Eaton EVMAF132X

Eaton Managed G4 Rack PDU, 0U, 39U, IEC-60309 input, 3m cord, 1ph, 7.4kW, 32A, 200-240V, 42 outlets (24)C13, (18)C39



### General specifications

<b>PRODUCT NAME</b>	Eaton Rack PDU G4
<b>CATALOG NUMBER</b>	EVMAF132X
<b>MODEL CODE</b>	PDU G4 MA 0U 309 32A 1P 24xC13,18xC39
<b>EAN</b>	3553340696923
<b>PRODUCT LENGTH/DEPTH</b>	1730 mm
<b>PRODUCT HEIGHT</b>	53 mm
<b>PRODUCT WIDTH</b>	52 mm
<b>PRODUCT WEIGHT</b>	2.9 kg
<b>WARRANTY</b>	3 year
<b>COMPLIANCES</b>	CB LVD Directive RoHS Directive WEEE Directive Packaging Directive EMC Directive
<b>CERTIFICATIONS</b>	IEC 62368-1 EN IEC 63000 CISPR 35/EN 55035 CE EAC UKCA Cm Ukr IEC/EN 61000-6-2 IEC/EN 61000-6-4 IEC 61000-3-11 IEC 61000-3-12



Powering Business Worldwide

## Electrical input

<b>INPUT CONNECTION</b>	IEC-60309 32A 1Ph
<b>WATTAGE</b>	7.4 kW max
<b>AMPERAGE RATING</b>	32 A
<b>INPUT VOLTAGE</b>	200-240V
<b>PHASE</b>	Single-phase
<b>CIRCUIT BREAKER</b>	(2) single-pole
<b>FREQUENCY RATING</b>	50/60 Hz
<b>CORD LENGTH</b>	3m

## Electrical output

<b>OUTLETS</b>	(24) C13, (18) C39
<b>NUMBER OF OUTPUTS C13</b>	24
<b>NUMBER OF OUTPUTS C19</b>	18
<b>NUMBER OF OUTPUTS (OTHER)</b>	18
<b>NUMBER OF OUTLETS WITH EARTH PIN</b>	42

## Technology & communications

**TYPE** Managed Rack PDU

**OUTLET CONTROL** Yes

### SPECIAL FEATURES

- Remote Site Management
- Versatile C39 outlet supports C14 or C20 power cord plug
- High retention outlets designed to securely fit standard power cords and support P-Lock power cords
- Cybersecurity standards UL 2900-1 and IEC 62443-4-2
- Hot-Swap network control module
- Network Cascading, connect up to 32 PDUs via network loop
- Power sharing between two network modules PDUs ensures constant access to PDU data & sensors
- 1% IEC Class 1 billing grade measurement accuracy
- Gigabit network card with 2x Gb ports
- Support protocols RestAPI, Modbus TCP, SNMP, LDAP, HTTPS
- 1% measurement accuracy at the outlet level (V, W, A)
- Outlets control for On/Off, reboot, and sequential start-up capabilities

**ETHERNET INTERFACE** Yes

**SERIAL INTERFACE** Yes

## Additional specifications

**OPERATING TEMPERATURE** 0° to 60°C (32° to 140°F)

### ACCESSORIES

- Rack PDU
- Rack mounting accessories
- Quickstart guide
- Safety Instructions

**MATERIAL** Aluminium

**COLOR** Black

<b>SNMP</b>	Yes
<b>MASS CONFIGURATION</b>	Yes

## Resources

<b>BROCHURES</b>	<a href="#">Rack PDU G4 Brochure EN</a>
<b>DECLARATIONS OF CONFORMITY</b>	<a href="#">EU declaration of conformity Rack PDU G4</a>

---

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**

---



**Eaton Corporation plc**

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

Follow us on social media to get the latest product and support information.

