



ENGLISH

Datasheet

Stock No: 245-0586

RS Pro Angle Type Cable Cutters, 137mm Overall Length, 1.02mm cutting capacity



Product Details

General Purpose ESD Cutters

High quality dissipative pliers and cutters having strong, pressed steel frames, riveted lap joints and precision ground jaws

Lightweight return springs give excellent handling and manipulation

An integral stop prevents handles from opening too far

Ideal for frequent but light duty use



Specifications:

Type	Angle
Overall Length	137mm
Materials Cut	Copper Wire
Cutting Capacity	1.02mm
Cut Type	Angle
Electrostatic Discharge Safe	Yes