

Datasheet

RS Pro Straight Panel Mount Bulkhead Fitting SMA Connector, jack, Solder Termination RG405

RS Stock No: **546-3153**



Product Details

RS Pro straight panel mount bulkhead fitting SMA connector features gold plating contact. This female connector is suitable use with semi-rigid and flexible coaxial cable. It is designed to provide high frequency performance at high power ratings in small diameters. It is also suitable for design and development work and where large quantity usage requires repeatability in performance.

Features and Benefits

- Gold plated contacts
- Suitable use with semi-rigid and flexible coaxial cable
- Solder termination method
- Designed to provide high frequency performance at high power ratings in small diameters

Specifications:

Body Orientation	Straight
Body Plating	Gold
Bulkhead	Yes
Cable Type	RG405
Contact Plating	Gold
Gender	Female
Mounting Type	Panel Mount
Operating Frequency	0 to 12.4 GHz, 0 to 18 GHz
Polarity	Normal
Size	Subminiature
Termination Method	Solder
Voltage Rating	450 V ac/dc
Type	SMA
VSWR (Voltage Standing Wave Ratio)	1.07 + 0.07