

Keyboard wired

00182682 "KC-600" Waterproof Keyboard, Cabled, black



Highlightstext:

- Washable and sturdy keyboard with classic key layout for all PC applications
- Protection against temporary immersion to IPX7
- Tilt adjustment allows the position to be adjusted for greatest comfort
- Laser-etched buttons for a high resistance to wear
- The full-format keypad provides you with the full-sized, familiar keyboard standard
- Control multimedia functions at the press of a button via the secondary assignment of Fn keys - without having to involve the tedious steps of changing system settings
- No sticky keyboard from spilt drinks or similar: simply rinse it under running water
- Non-slip rubber feet for secure stand
- USB port

System Requirements:

- Operating system: Windows 11/10/8/7

Note for Consumers:

- Wash by hand only, do not wash in the dishwasher
- Do not use any aggressive cleaners
- Do not immerse USB cable in water
- After cleaning, allow to dry in a well ventilated room for at least 12 hours

Technical characteristics:


- Colour: Black
- Keyboard Layout: QWERTZ (German)
- Product Division: PC & Notebook
- Shade of colour: Black
- Connection: Cable
- Connection: USB-Typ-A-Plug
- Compatible operating systems: Windows 11/10/8/7
- Special features: Folding feet/Water resistant
- Key label: Laser engraving
- Key technology: Rubber Dome
- Model: Full format keyboard
- Number of Keys: 105
- Type: Office
- Cable Length: 180 cm
- Depth: 14.4 cm
- Height: 2.9 cm
- Width: 45 cm

Delivery:

- 1 "KC-600" keyboard
- 1 instruction manual

Keyboard wired

00182682 "KC-600" Waterproof Keyboard, Cabled, black

 4 047443 425676	Brand	Item-no.	VE	MB	SRP
	<i>hama</i>	00182682	20	1	EUR 39,99