


REV	DESCRIPTION	DATE
-----	-------------	------



NOTE:

1. MAXIMUM ELECTRIC CURRENT:

A.W.G.	22	20	18	16
AMP.	9	12	17	18
2. MAXIMUM ELECTRICAL RATING:
75°C 600 VOLTS MAX.
3. INSULATION MATERIAL: VINYL
4. INSULATION COLOR: RED
5. TERMINAL MATERIAL: COPPER
6. WIRE RANGE: 22-16A.W.G. (0.5-1.5mm²)

Tolerance Unless Otherwise Specified	
0 >	MM ± ANGLE
>	MM ± 0° REF ±
>	MM ± ° ±
>	MM ± ° ±

NAME	VINYL-INSULATED BLADE TERMINALS				UNIT	mm	
PART NO.	DBVY1-13@	MATERIAL			APPROVE		
NUMBER	TNV-1017	SCALE	SHEET	PAGE	CHECKED		
DATE	09/07/2005	4 : 1	1-0	1 OF 1	DRAWN		

1
2
3
4
5
6

1
2
3
4
5
6

A B C D E F G H