
ball valve VZBE-3/4-T-63-D-2-M-V15V15 Part number: 4745218 ☆ Core product range

Stainless steel, manual version, 2/2-way, nominal width 3/4", PN63, ASME B1.20.1 - NPT.

Festo is only a retailer of this product, not the manufacturer.





FESTO

Data sheet

Feature	Value
Design structure	2-way ball valve with hand lever
Type of actuation	mechanical
Sealing principle	soft
Assembly position	Any
Mounting type	Line installation
Process valve connection	3/4 NPT
Switching position indicator	Slot direction = flow direction
Inside diameter	20 mm
Nominal diameter DN	20
Valve function	2/2
Flow direction	reversible
Nominal pressure of process valve	63
Breakaway torque at differential pressure, nominal pressure, process valve PN	7.5 Nm
Based on the standard	ASME B1.20.1
Medium	Vapour
	Compressed air in accordance with ISO8573-1:2010 [-:-:-]
	Inert gases
	Water
	Neutral fluids
Medium temperature	-20 200 °C
Flow rate Kv	15.6 m3/h
Materials note	Contains PWIS substances
	Conforms to RoHS
Material housing	Stainless steel casting
Material number for housing	1.4408
Material seat seal	PTFE
Material seals	PTFE
Material ball	Stainless steel casting
Material number for ball	1.4408
Material shaft	High alloy steel, non-corrosive
Material number for shaft	1.4401
Product weight	500 g
Authorisation	CRN
Corrosion resistance classification CRC	3 - High corrosion stress