



ENGLISH

Datasheet

**RS Pro Anti surge T HBC fuse, 2A 5 x 20mm BP**

RS Stock No: **563-609A**



## Product Details

RS Pro anti surge high breaking capacity fuse is current rated for 2 A. This T-speed, Littelfuse time lag ceramic body cartridge fuse is ideal for applications when surge withstand is required.

**Specifications:**

Body Material	Ceramic
Breaking Capacity (at Maximum Voltage Rating)	1500 A
Current Rating	2 A
Diameter	5.2 mm
Fuse Speed	T
High Rupture Capacity	Yes
Includes Indicator	No
Maximum Operating Temperature	+125°C
Minimum Operating Temperature	-55°C
Operating Temperature Range	-55 to +125°C
Overall Dimensions	5.2 x 20 mm
Overall Length	20 mm
Resistance	0.0499 Ω
Size Designation	Miniature
Voltage Rating	250 V ac
Standards Met	CSA Acceptance, UL Recognised, RoHS Compliant, BSI, PSE, KTL, CCC, CQC, VDE, SEMKO