

# tesa® 4311

## Product Information



tesa® 4311 is a conformable masking tape based on a fine crepe paper backing in white color and a natural rubber adhesive.

### Product Description

tesa® 4311 is a conformable masking tape based on a fine crepe paper backing coming in white color and a natural rubber adhesive. The essential masking tape is suitable for light duty spray painting and general purpose applications like, holding, sealing, fixing. It provides a temperature resistance up to 60°C and is suitable for subsequent oven drying.

### Product Features

The white crepe paper backing ensures a good conformability.

The natural rubber adhesive system features good adhesion to multiple surfaces as well as a good tack.

### Application Fields

- tesa® 4311 is suitable for light duty spray painting and multi-purpose masking applications.
- It provides temperature resistance up to 60°C and is suitable for subsequent oven drying.
- The tape is hand-tearable

### Technical Information (average values)

The values in this section should be considered representative or typical only and should not be used for specification purposes.

### Product Construction

- |                    |                       |                   |        |
|--------------------|-----------------------|-------------------|--------|
| • Backing material | slightly-creped paper | • Total thickness | 120 µm |
| • Type of adhesive | natural rubber        |                   |        |

### Properties/Performance Values

- |                       |         |                    |           |
|-----------------------|---------|--------------------|-----------|
| • Elongation at break | 6 %     | • Hand tearability | very good |
| • Tensile strength    | 23 N/cm |                    |           |

### Adhesion to Values

- |         |          |
|---------|----------|
| • steel | 2.8 N/cm |
|---------|----------|

# tesa<sup>®</sup> 4311

## Product Information

### Disclaimer

tesa<sup>®</sup> products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa<sup>®</sup> product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.



For latest information on this product please visit <http://l.tesa.com/?ip=4311PV0>