

Circular Saw XGT®

HS013G

40Vmax, 2100 min⁻¹, 415 mm

Model HS013G is powered by a 40V XGT® Li-Ion battery.

Model HS013G achieves high power similar and superior to corded models allowing for cutting through beams and sleepers with a thickness of up to 160mm in a single stroke. Feature and Benefits: EFFICUT saw blade, Compatible with Auto-start wireless system (AWS), Lightweight design and enhanced manoeuvrability.



Technical specifications

Nominal Battery Voltage	40 V
Voltage XGT	✓
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Brushless Motor	✓
No load speed	2100 min ⁻¹
Max. Cutting Depth at 90°	160 mm
Max. Cutting Depth at 45°	106 mm
AWS ready	✓
Sound Power Level (L _{WA})	106 dB(A)
Sound Pressure Level (L _{pA})	98 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Product Dimensions (L x W x H):	606 x 233 x 476 mm
Tool weight with battery	11,0 - 12,0 kg
Max. Bevel Range (Right)	0 - 45 °

User benefits

- Auto-start Wireless System (AWS) connects to compatible vacuum cleaners with Bluetooth
- Soft start suppresses start-up reaction for more control and better accuracy
- Anti-restart function minimises accidental start-up
- Electric brake for maximum productivity and increased operator safety
- Lightweight & high power

Link to product - www.makita.uk.com



Related products

Other

User manual

Parts drawing