



1. CABLE DIAMETER RANGE, 4.6 mm TO 7.9 mm, CABLE FITTING ONLY, SEE APPLICATION SPECIFICATION FOR PLUG TERMINATION INFORMATION
2. THIS PRODUCT HAS NOT COMPLETED VALIDATION TESTING.
3. PARTS PACKAGED UNASSEMBLED IN POLYBAG.
4. GEOMETRY CAN VARY.
5. ELASTOMER SEAL IS SECURED TO HOUSING WITH ADHESIVE.

SHIELDED	24-26 AWG STRANDED	1738607-4
	24-26 AWG SOLID	1738607-3
UNSHIELDED	24 AWG STRANDED	1738607-2
	24 AWG SOLID	1738607-1
DESCRIPTION	CONDUCTOR TYPE	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN R.L. KOLLER 25MAR04	Tyco Electronics Harrisburg, PA 17105-3608	
DIMENSIONS: mm		CHK J. LANDIS 26MAR04	NAME PLUG ASSEMBLY INDUSTRIAL CIRCULAR ETHERNET CONNECTOR	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±0.3 1 PLC ±0.2 2 PLC ±0.10 3 PLC ± 4 PLC ± ANGLES ±° FINISH		APVD S. HEADER 17JUN05	SIZE A2	
MATERIAL -		PRODUCT SPEC 108-2198	CAGE CODE 00779	
		APPLICATION SPEC 114-13136	DRAWING NO 1738607	
		WEIGHT -	RESTRICTED TO -	
		CUSTOMER DRAWING	SCALE 5:2	
			SHEET 1 OF 1	
			REV C	