



Connectors > Connector Accessories > Connector Hardware



Connector Hardware Accessory Type: **Female Screwlock**

Hardware Accessory Function: **Latching, Locking & Retention**

Features

Product Type Features

Connector Hardware Accessory Type	Female Screwlock
Hardware Accessory Function	Latching, Locking & Retention

Mechanical Attachment

Thread Size	4-40 UNC 2A (Male), M3 (Female)
-------------	---------------------------------

Dimensions

Thread Length	9.7 mm[.382 in]
Product Feature Length	15.9 mm[.62 in]

Packaging Features

Packaging Method	Carton
Packaging Quantity	1000

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) SVHC > Threshold: Pb (4% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.



Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 829261-8
HD FEMALE SCREWLOCK

Also in the Series | AMPLIMITE Kit



Connector Caps & Covers(2)



Connector Hardware(91)



Connector Seals & Cavity Plugs(4)



Connector Strain Relief(126)

Customers Also Bought



TE Part #770022-1
12P UMNLI IN-LNE PLUG HSG KIT




TE Part #1-1337443-0
BNC Str Jk Hex 75Ohm Nickel Pltd RG59B/U



TE Part #350781-1
06P UMNL CAP HSG



TE Part #969028-3
TAB A 1.6x0.6 CONTACT CS SWS Au



TE Part #9-160313-2
250 PIDG FASTON REC



TE Part #9-1768017-3
EET-0820P-8A



TE Part #1747053-1
40 P HDR ASSY - V TYPE PC.I/O CONN.



TE Part #207446-3
SEALING CAP ASSY,SZ 23,CPC



TE Part #1102837-1
HF-EMV-K.8.AG.N



TE Part #1108821-1
HF8.STO.2.M32+2x95

Documents

Product Drawings
HD-20SCHRAUB-SICHRG

English

CAD Files
Customer View Model
ENG_CVM_CVM_1-828101-1_O.2d_dxf.zip

English

3D PDF

3D

Customer View Model
ENG_CVM_CVM_1-828101-1_O.3d_igs.zip

English

Customer View Model
ENG_CVM_CVM_1-828101-1_O.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications



Product Specification

English