







REV.	DESCRIPTION	DATE	DRAWN
A	New	15.05.2019	Cherry



### Specifications

#### Electrical

- Current rating: 1.5A
- DC resistance: 0.1Ω max.
- Insulation resistance: 500MΩ min.
- Contact resistance: 20mΩ max.
- Withstanding voltage: 1000V AC / Minute

#### Materials

- Plastic Body: Fireproof ABS UL-94V0
- RJ45 Jack: 8P8C 6μ" Gold
- RJ12 Jack: 6P6C 6μ" Gold
- PCB: FR-4 UL-94V0
- BNC Body: Zinc Casting; Ni plated
- Leather Bag: PVC



#### Mechanical Requirements

- RJ45 Jack Insertion Cycle: 2000 cycles min.
- RJ12/DEC Jack Insertion Cycle: 2000 cycles min.
- Operating temperature: -40°C to +70°C

#### Cable Tester

- Used for RJ45, RJ45/Shielded, RJ45/Keyed, RJ12, RJ12/DEC, RJ11, BNC
- This LAN-Tester can test
- Open Shorted Crossed Reversed Transposed Split Non-Pair Wiring
- Power: DC-9V Battery
- Remote Box can remotely test LAN-cable up to 1000 FT
- Can test Grouding
- There are one Spare Battery& two 6 to 4 Inserts in the Remote Box

E-tec 2019 © - all rights reserved www.e-tec.asia



UNIT	mm	GENERAL TOLERANCE		DRAWN	Cherry	DATE	15.05.2019			
	SCALE	Free	X.° ±		X. ±		CHECK	Kent	DATE	15.05.2019
			.X° ±		.X ± 1					
			.XX° ±		.XX ± 1					
			.XXX° ±		.XXX ±					
		APPROVE	SH	DATE	15.05.2019					

DWG. NO.	LANTESTER SFXB	SHEET 1/1
REV.	A	
SERIES NO.	LANTESTER SFXB	

**LAN Tester**