

rotronic

Datenblatt - Fiche technique - Data sheet

11.02.8873




ROLINE USB 3.0 Kabel, A ST – Micro B ST, 0,8m

ROLINE USB 3.0 Cable, A M – Micro B M, 0,8m

**ROLINE USB 3.0 Cable, USB Type A M – USB Type Micro B M,
0.8 m**


RoHS COMPLIANT



NOTES:

1. CABLE:UL20276 USB3.0 CABLE(28AWG*1P+EAM)*2+28AWG*1P +24AWG*2C+AEB(CU WIRE, AM BRAID) OD=5.5MM COLOR:BLACK,
2. CONN:USB3.0 A/M INSULATION:BLUE SHELL NICKEL-PLATED, CONTACT GOLD-PLATED 30U"
3. CONN:MICRO USB 3.0 B MALE INSULATION:BLACK, SHELL Nickel-PLATED, CONTACT GOLD-PLATED 30U"
4. OUTER MOLD:PVC 45P BLACK

WIRE ADDRESS



ELECTRICAL TEST:

1. 100% TEST OPEN SHORT MIS-WIRE;
2. INSULATION RESISTANCE:2M OHM MIN.

ITEM NO	11.02.8873	Draw	Date	2013-07-26	rotronic	D		
DESC.	ROLINE USB 3.0 Cable, A M / Micro B M, 0.8m, black	Check	Date			C		
origina1NO.	Unit (MM)	Approval	Date			B		
						VER. A	REVISE	Date