


# differential pressure regulator

## LRL-1/4-QS-6

Part number: 153514

FESTO

Without manometer, with male thread and QS plug connector.



### Data sheet

Feature	Value
Controller function	Differential pressure, constant with return flow
Pneumatic connection, port 1	G1/4
Pneumatic connection, port 2	QS-6
Mounting type	Threaded
Nominal flow rate open	241 l/min
Pressure regulation range	2 ... 6 bar
Inlet pressure 1	0 ... 9 bar
Ambient temperature	0 ... 60 °C
Material housing	PBT-reinforced
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Actuator lock	Knurled screw with lock nut
Assembly position	Any
Design structure	directly-controlled piston regulator with looped-through compressed air supply
Nominal flow rate closed	240 l/min
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Product weight	38 g
Material of threaded plug	Brass Nickel plated
Materials note	Conforms to RoHS
Material of threaded seal	PTFE