# Slide Compound Mitre Saw LXT®

# DLS110

18V X2 • 260 mm • 4 400 min$^{-1}$

**Efficient brushless cordless saw.**

Powered by 2 X 18V LXT® Batteries, which makes this saw powerful. The Rail-forward design enables to be placed against a wall for maximising work space. Automatic torque Drive Technology (ADT) adjusts speed and torque during operation for optimum performance. Large turn base supports workpiece securely.



## Technical specifications

| | |
|---|---|
| Voltage LXT | ✓ |
| Max. kerf thickness of the saw blade | 3,2 mm |
| Capacity 90° | 91 x 279 / 68 x 310 mm |
| Capacity 45° | 91 x 197 / 68 x 218 mm |
| Max. Mitre Range (Left) | 60 / 60 ° |
| Capacity 45° left | 58 x 279 / 42 x 310 mm |
| Max. Bevel Range (Left) | 48 / 48 ° |
| Bevel capacity right 45° | 43 x 279 / 29 x 305 mm |
| Blade Diameter | 260 mm |
| Bore Size (Arbor Diameter) | 30 mm |
| Nominal Battery Voltage | 2 x 18 V |
| No load speed | 4400 min$^{-1}$ |
| Sound Power Level ($L_{WA}$) | 102 dB(A) |
| Sound Pressure Level ($L_{pA}$) | 92 dB(A) |

## User benefits

- Battery protection system automatically shuts off power when the battery level is low
- Brushless maintenance-free and long-life motor
- Battery protection system automatically shuts off power when the battery level is low
- Brushless maintenance-free and long-life motor
- Large turn base supports workpiece securely for increased stability
- Integrated guide fences for increased rigidity and high cutting accuracy
- Single sliding system enables smooth operation to produce superior cuts
- Front knob for easy bevel angle adjustment
- Holders are provided on both sides of the tool to hold long workpieces horizontally
- Oversized trigger switch for better fit, added comfort and easier operation

**Link to product - www.makitauk.com**

# Related products

## Other

User manual

Parts drawing