



## Main

Range	Thalassa
Accessory / separate part category	Mounting accessory
Product or component type	Technical upright
Device application	Multi-purpose
Enclosure nominal dimensions	-
Mounting support	Direct fixing on the rear inserts Step slide
Range compatibility	Thalassa PLA
Device composition	2 upright
Material	Steel

## Complementary

Surface finish	Zinc coated
Fixing mode	Bosses inserts - screw type M8 - rear of enclosure location
Adjustment	Adjustable in height every 2.5 mm with quarter-turn nuts
Height	750 Mm nominal: 625 Mm real:
Width	45 Mm
Depth	34 Mm
Thickness	2 Mm
Cut-out dimensions	11 x 13 mm

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	2.0 Kg
Package 1 Height	4 Cm
Package 1 width	6 Cm
Package 1 Length	62.5 Cm

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

### Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status :	Commercialised
-----------------------	----------------