


FEATURES

- **Dimming Operations:** Supports DALI2, Push Dimming, and PWM for versatile lighting control
- **Driver Current:** 2.5 A ensures efficient power delivery to connected LEDs
- **Input Voltage:** Compatible with 100 to 277 V AC, suitable for a wide range of installations
- **IP Rating:** IP20 rated for indoor use, providing basic protection against dust
- **Operating Mode:** Constant Voltage operation for stable LED performance
- **Terminal Type:** Screw terminals for secure and easy connections

RS PRO 60W LED Driver, 24V Constant Voltage

RS Stock No: 642-772



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO LED Driver is designed to provide a reliable power source for LED lighting systems. With a maximum output power of 60W and an output voltage of 24V, it ensures consistent performance for various lighting applications. The driver supports multiple dimming operations, including DALI2, Push Dimming, and PWM, offering flexibility and control in lighting environments.

General Specifications

Dimming Operation	DALI2, Push Dimming, PWM
Number of Outputs	1
Operating Modes	Constant Voltage
Primary Type	AC
Product Type	LED Driver
Sub Type	Constant Voltage LED Driver
Terminal Type	Screw

Electrical Specifications

Driver Current	2.5 A
Input Voltage	100-277 V ac
Input Voltage Type	AC
Maximum Output Power	60 W
Output Voltage	24 V

Protection Category

IP Rating	IP20
-----------	------

Approvals

Standards/Approvals	CE, EN55015, EN61000-3-2, EN61000-3-3, EN61000-4-2,3,4,5,6,11, EN61347-1, EN61347-2-13, EN61547, EN62493, UL8750
---------------------	--