

## Datasheet

# RS Pro LCD Digital Panel Multifunction Meter, 22mm x 44.8mm

RS Stock No: **896-6995**



## Product Details

RS Pro LCD digital panel multifunction meter is used to indicate 7 digit total value or rate on LCD display. It has two keys on front panel. The meter comes with alarm facility for both rate indicator and totalizer.

## Features and Benefits

- 7-digit (6.5 mm) LCD display
- 2 keys on front panel
- Panel mount
- Wide input signal sensing range: 0.01 Hz to 20 kHz
- Wide totalizer range from 1 to 9999999
- Wide rate range from 1 to 999999
- pre-scaling facility for rate indicator
- Alarm facility for both rate indicator and totalizer
- Password enabled
- Signals over-range displayed



ENGLISH

### Specifications:

|                     |                  |
|---------------------|------------------|
| Approvals           | RoHS Compliant   |
| Meter Type          | Digital          |
| Cutout Height       | 22 mm            |
| Cutout Width        | 44.8 mm          |
| Depth               | 62 mm            |
| Maximum Temperature | +55°C            |
| Measurement Range   | 0 to 9999999     |
| Minimum Measurement | 0                |
| Minimum Temperature | -10°C            |
| Number of Digits    | 7                |
| Digit Height        | 6.5 mm           |
| Display Type        | LCD              |
| IP Rating           | IP40, IP20, IP30 |
| Mounting Type       | Panel Mount      |