



PM Panel|Mate™ AT



4 Hole Flange Mount Receptacles

Available in 2, 3, 4, 6, 8 and 12 Position/Size 16, 13A

Our **PanelMate™ AT 4-Hole Flange Mount Receptacle** is a two-piece, sonically-welded flange design connector series for electrical enclosure applications requiring an externally operated connection with pass through holes. The durable welded flange assures users with a secure and convenient panel mount option for use with the full range of **AT Series™** receptacles.

The **AT Series™** connector design incorporates an integral latching system that ensures a definitive electrical and mechanical connection. Connector housings are manufactured with a durable, UV resistant, thermoplastic material with dielectric/mechanical properties and environmentally RoHS compliant. The sealing system is comprised of front and rear silicone seals, multi-sealing perimeter against environmental ingress. Contacts are derived from quality copper alloy to ensure an electrically-reliable connection. **AT Series™** connectors are compatible with other existing standard products industry-wide.

Applications: Heavy Duty, Transportation, Marine, Diagnostic, Military, Alternative Energy, Agricultural, and other demanding interconnect architectures

Key Features

- Available in positions 2, 3, 4, 6, 8, 12
- Size 16 contacts with 13A continuous capacity
- IP67 rated (mated)
- Silicone elastomer rear seals
- Rectangular, thermoplastic housing
- Secondary wedge locks secure contacts (sold separately)
- Thermoplastic housing with integrated latch for mating
- Custom color options available



AT Series™



Sample
AT Series™ P/N
AT04-2P



Sample
AT Series™ P/N
AT04-6P

Our **PanelMate™** brand meets all the performance criteria and specifications of the **AT Series™**, and is available in a wide variety of custom colors.



A Series™ Family



Standard products. Custom solutions
Customer Service +1 800 394 7732



PanelMate™ AT 4 Hole Flange Mount Receptacles

Image	Part Number	Description	Contact Size	Amps/Voltage	AWG
 AT04-2P-L012	AT04-2P-L012	2 Pos., Receptacle, Flange Mount Connector, Pin, Gray	16	13/250	14-20
	AT04-3P-L012	3 Pos., Receptacle, Flange Mount Connector, Pin, Gray	16	13/250	14-20
	AT04-3P-LE08	3 Pos., Receptacle, Flange Mount Connector, Pin, Gray, w Shrink Boot Endcap	16	13/250	14-20
	AT04-3P-LE12	3 Pos., Receptacle, Flange Mount Connector, Pin, Black, w Shrink Boot Endcap	16	13/250	14-20
	AT04-3P-CL03	3 Pos., Receptacle, Flange Mount Connector, Pin, Gray, Reduced Diameter Seal	16	13/250	16-20
	AT04-3P-CL06	3 Pos., Receptacle, Flange Mount Connector, Pin, Black, Reduced Diameter Seal	16	13/250	16-20
	AT04-4P-L012	4 Pos., Receptacle, Flange Mount Connector, Pin, Gray	16	13/250	14-20
 AT04-4P-L012	AT04-4P-LE11	4 Pos., Receptacle, Flange Mount Connector, Pin, Black, w Endcap	16	13/250	14-20
	AT04-4P-CL03	4 Pos., Receptacle, Flange Mount Connector, Pin, Gray, Reduced Diameter Seal	16	13/250	16-20
	AT04-4P-CL06	4 Pos., Receptacle, Flange Mount Connector, Pin, Black, Reduced Diameter Seal	16	13/250	16-20
	AT04-6P-L012	6 Pos., Receptacle, Flange Mount Connector, Pin, Gray	16	13/250	14-20
	AT04-6P-CL06	6 Pos., Receptacle, Flange Mount Connector, Pin, Black, Reduced Diameter Seal	16	13/250	16-20
	AT04-8PA-CL03	8 Pos., Receptacle, Flange Mount Connector, Pin, Gray, Reduced Diameter Seal, Keyed A	16	13/250	16-20
 AT04-4P-L012	AT04-8PA-CL06	8 Pos., Receptacle, Flange Mount Connector, Pin, Black, Reduced Diameter Seal, Keyed A	16	13/250	16-20
	AT04-8PA-L012	8 Pos., Receptacle, Flange Mount Connector, Pin, Gray, Keyed A	16	13/250	14-20
	AT04-8PB-L012	8 Pos., Receptacle, Flange Mount Connector, Pin, Black, Keyed B	16	13/250	14-20
	AT04-8PC-L012	8 Pos., Receptacle, Flange Mount Connector, Pin, Green, Keyed C	16	13/250	14-20
	AT04-8PD-L012	8 Pos., Receptacle, Flange Mount Connector, Pin, Brown, Keyed D	16	13/250	14-20
	AT04-8PA-LE11	8 Pos., Receptacle, Flange Mount Connector, Pin, Black, Keyed A, w Endcap	16	13/250	14-20
	AT04-12PA-L012	12 Pos., Receptacle, Flange Mount Connector, Pin, Gray, Keyed A	16	13/250	14-20
	AT04-12PB-L012	12 Pos., Receptacle, Flange Mount Connector, Pin, Black, Keyed B	16	13/250	14-20
	AT04-12PC-L012	12 Pos., Receptacle, Flange Mount Connector, Pin, Green, Keyed C	16	13/250	14-20
	AT04-12PD-L012	12 Pos., Receptacle, Flange Mount Connector, Pin, Brown, Keyed D	16	13/250	14-20
	AT04-12PA-LE07	12 Pos., Receptacle, Flange Mount Connector, Pin, Gray, Keyed A, w Endcap	16	13/250	14-20
	AT04-12PB-LE07	12 Pos., Receptacle, Flange Mount Connector, Pin, Black, Keyed B, w Endcap	16	13/250	14-20
 AT04-6P-L012	AT04-12PC-LE07	12 Pos., Receptacle, Flange Mount Connector, Pin, Green, Keyed C, w Endcap	16	13/250	14-20
	AT04-12PD-LE07	12 Pos., Receptacle, Flange Mount Connector, Pin, Brown, Keyed D, w Endcap	16	13/250	14-20
	AT04-12PA-LE14	12 Pos., Receptacle, Flange Mount Connector, Pin, Black, Keyed A, w Endcap	16	13/250	14-20
	AT04-12PA-BL04	12 Pos., Receptacle, Flange Mount Connector, Pin, Gray, Keyed A, w Endcap	16	13/250	14-20
	AT04-12PB-BL04	12 Pos., Receptacle, Flange Mount Connector, Pin, Black, Keyed B, Enhanced Key	16	13/250	14-20
	AT04-12PC-BL04	12 Pos., Receptacle, Flange Mount Connector, Pin, Green, Keyed C, Enhanced Key	16	13/250	14-20
	AT04-12PD-BL04	12 Pos., Receptacle, Flange Mount Connector, Pin, Brown, Keyed D, Enhanced Key	16	13/250	14-20
	AT04-12PA-BL05	12 Pos., Receptacle, Flange Mount Connector, Pin, Gray, Keyed A, Enhanced Key, w Endcap	16	13/250	14-20
	AT05-12PB-BL05	12 Pos., Receptacle, Flange Mount Connector, Pin, Black, Keyed B, Enhanced Key, w Endcap	16	13/250	14-20
	AT05-12PC-BL05	12 Pos., Receptacle, Flange Mount Connector, Pin, Green, Keyed C, Enhanced Key, w Endcap	16	13/250	14-20
	AT05-12PD-BL05	12 Pos., Receptacle, Flange Mount Connector, Pin, Brown, Keyed C, Enhanced Key, w Endcap	16	13/250	14-20
	AT04-12PA-BL08	12 Pos., Receptacle, Flange Mount Connector, Pin, Black, Keyed A, Enhanced Key	16	13/250	14-20
 AT04-08PA-L012	AT04-12PA-CL03	12 Pos., Receptacle, Flange Mount Connector, Pin, Gray, Keyed A, Reduced Diameter Seal	16	13/250	16-20
	AT04-12PB-CL03	12 Pos., Receptacle, Flange Mount Connector, Pin, Black, Keyed B, Reduced Diameter Seal	16	13/250	16-20
	AT04-12PC-CL03	12 Pos., Receptacle, Flange Mount Connector, Pin, Green, Keyed C, Reduced Diameter Seal	16	13/250	16-20
	AT04-12PD-CL03	12 Pos., Receptacle, Flange Mount Connector, Pin, Brown, Keyed D, Reduced Diameter Seal	16	13/250	16-20
	AT04-12PA-CL06	12 Pos., Receptacle, Flange Mount Connector, Pin, Black, Keyed A, Reduced Diameter Seal	16	13/250	16-20

For more information, contact: Customer Service, +1 800 394 7732, csr@amphenol-sine.com