

8000 A 1G

Circlip pliers for external retaining rings

Code	ETIM
6700220	EC002228
EAN	UNSPSC
4010886670026	27-11-21-10
Country of origin	eCl@ss
Austria	21-04-03-01
Customs tariff number	
82032000	



Article description

- For shafts without groove
- For self-locking Seeger grip rings and for self-locking Benzing clamping rings
- Similar to DIN 5254 Form A
- A 0G - A 1G = 30° angled jaws
- A 2G = straight tips
- With opening spring and adjusting screw to limit opening
- High degree of assembly reliability, the limit opening rules out any over-tensioning of the smallest of retaining rings
- Forged GEDORE chrome-vanadium special hardened and tempered steel
- Precision machined, oil hardened and annealed
- Black, with red dipped handles

Article information

Contents (Qty of pieces)	1	Length of head	40 mm
Net weight [kg]	0,098 kg	Tip diameter	1,1 mm
Total length [mm]	140 mm	Handle design	dip-insulated
Total width [mm]	70 mm	Shaft diameter for Benzing clamping rings	3,0-11,0
Total height [mm]	11 mm	Shaft diameter for Seeger grip rings	4,0-9,0
Surface	Black varnished	Opening spring present	yes
Material	Chrome-vanadium steel	Hardening process	oil-hardened and tempered
Design non-sparking	No	Joint types	applied joint