


11111
Abrasive shaft-mounted wheels, abrasive pink corundum grains, ceramic bonded, rounded, cone-shaped
EN 12413

For universal use

 shaft \varnothing 6 x 40 mm

	art.	\varnothing mm	h mm	max. rpm Lo=13 mm	
111110010	11111 10X20	10	20	86.600	AR60P5V
111110015	11111 15X30	15	30	51.000	AR46P5V
111110016	11111 16X45	16	45	31.400	AR46P5V
111110020	11111 20X28	20	28	41.500	AR46P5V
111110021	11111 20X40	20	40	29.000	AR46P5V
111110030	11111 30X50	30	50	15.100	AR36/46P5V

