


E40516



Process adapter SMS 1145

ADAPT SMS1145 DN100



Application	
Design	for volumetric flow meters SMF
Application	food and beverage industry; hygienic systems
Pressure rating	16 bar 1.6 MPa
Tests / approvals	
Pressure Equipment Directive	A possible classification to PED depends on the application and has to be carried out by the user / operator.
Safety instructions	The compatibility between medium and product material has to be checked in all applications.
Mechanical data	
Weight [g]	6619.4
Materials	stainless steel (316L/1.4404)
Nominal diameter	DN100 (4")
Sensor connection	ifm-specific device flange

E40516



Process adapter SMS 1145

ADAPT SMS1145 DN100

Process connection	SMS 1145
Process connection suitable for pipe standard	(ISO 2037); (DIN EN 10357 Series D); (BS 4825 Part 1)
Surface characteristics Ra/Rz of the wetted parts	Ra ≤ 0.4 μm
Accessories	
Items supplied	screws 12
Remarks	
Pack quantity	2 pcs.