

Features

- *Conductor
Material: 100%
copper wires*
- *Jacket Material:
PVC, black*
- *Cable Length:
10M*
- *Easy to install
and reliable
connection*
- *Color: Black*

RS PRO Telephone Cable

RS Stock No.: 0707863



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against

demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

This is a RJ12 6P6C to 12 6P6C data cable (Also called RJ11 6P6C Cable) for both data and voice use, overall length is 10M.

Both ends are durable RJ12 6P6C modular connector;

Straight-through pin out for both data and voice use;

100% copper 6 conductors black wire;

It can be used as a regular telephone cord, fax cable, DSL modem cable, cash drawer cable and also in printer system, radio system, control system etc.

General Specifications

<i>Number of Strands</i>	<i>6</i>
<i>Conductor Strand Type</i>	<i>Stranded</i>
<i>Terminated/Unterminated</i>	<i>Terminated; Unterminated</i>
<i>Connector Type</i>	<i>Male RJ12</i>
<i>Connector B</i>	<i>Male RJ12</i>
<i>Connector A</i>	<i>Male RJ12</i>
<i>Outer Sheath Material</i>	<i>PVC;</i>
<i>Sheath Colour</i>	<i>Black</i>
<i>Conductor Material</i>	<i>Bare Copper</i>
<i>Drain Wire</i>	<i>No</i>
<i>Fire Behaviour</i>	<i>Flame Retardant.</i>

Mechanical Specifications

<i>Length</i>	<i>10m</i>
<i>Outer Diameter</i>	<i>2.4*6.8mm</i>
<i>Sheath Thickness</i>	<i>0.6mm</i>

<i>Insulator Diameter</i>	0.9mm +/-0.05
<i>American Wire Gauge</i>	28AWG
<i>Cross Sectional Area</i>	0.079mm ²
<i>Size of Strands</i>	7/0.12mm, 28AWG
<i>Core Strands</i>	7/0.12mm

Approvals

<i>Compliance/Certifications</i>	RoHS, Reach
<i>Declarations</i>	RoHS, Reach

