



Main

Range of product	Actassi
Product or component type	Plinth raiser
Accessory / separate part category	Mounting accessory
Colour	Grey (RAL 9011)

Complementary

Material	Textured epoxy-polyester powder sheet steel
Mounting location	Fixing to the floor
Adjustment	Feet adjustable from 0 to 60 mm with holes Adjustable in height from 200 mm to 350 mm in steps of 25 mm
Permanent permissible load	1000 Kg static load
Range compatibility	Actassi SF Actassi VDS Actassi VDA
Product destination	Rack
Number of rack unit	24U 42U
Height	200...350 Mm
Width	800 Mm
Depth	1000 Mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	21.000 Cm
Package 1 Width	80.000 Cm
Package 1 Length	105.000 Cm
Package 1 Weight	12.756 Kg
Unit Type of Package 2	P12
Number of Units in Package 2	8
Package 2 Height	170.000 Cm
Package 2 Width	80.000 Cm
Package 2 Length	120.000 Cm
Package 2 Weight	110.000 Kg

Offer Sustainability

Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant
End of life manual availability	No need of specific recycling operations