

Terminal boxes KL without gland plate – KL 1527.510



Product description

Material:

- Enclosure: Sheet steel
- Cover: Sheet steel, all-round foamed-in PU seal

Surface finish:

- Enclosure and cover: Dipcoat primed, powder-coated on the outside, textured paint

Colour:

- RAL 7035

Protection category IP to IEC 60 529:

- IP 66

Protection category NEMA:

- NEMA 4

Supply includes:

- Enclosure with cover
- Quick-release fastener including plastic bushes

Packs of:

- 1 pc(s).

EAN:

- 4028177251328

Customs tariff number:

- 94032080

Product features



Dimensions:

- Width: 800 mm
- Height: 200 mm
- Depth: 120 mm



Weight:

- 6.8 kg


Approvals**Approvals:**

-  [Bureau Veritas \(EN\)](#)
-  [VDE \(EN, DE\)](#)
-  [UL \(EN\)](#)
-  [TÜV \(EN\)](#)
-  [TÜV \(DE\)](#)
-  [Russian Maritime Register of Shipping \(RU, EN\)](#)
-  [Lloyds Register of Shipping \(EN\)](#)
-  [C-UL \(EN\)](#)
-  [CSA \(EN\)](#)
-  [Germanischer Lloyd \(EN\)](#)

Declarations:

-  [Manufacturer's declaration \(EN, DE\)](#)
-  [Declaration of conformity \(EN, DE\)](#)

Downloads**Documentation:**

-  [Instructions \(EN, DE\)](#)

CAD drawings:

- Request