


Technical data


KR30

Cam follower with shaft



Needle roller bearing, cam follower, with cage, slot for screwdriver, oil hole, spherical outer ring

VISUAL (S)



PRODUCT DEFINITION

Brand	NTN
D - External diameter	30 mm
d1 - Stud diameter	12 mm
C - Width of bearing, drawn cup or outer ring	14 mm
F - Under roller diameter	15 mm
B - Bearing/Inner ring width	15 mm
B1 - Total stud length	40 mm
B2 - Stud rod length	25 mm



NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

PRODUCT DEFINITION	
G - Stud thread designation	M12X1.5
G1 - Thread length of the stud	13 mm
B3 - Distance between washer face and radial lub hole	6 mm
C1 - Distance between roller face and washer face	0,6 mm
n - Axial lubrication hole diameter	6 mm
a - Radial lubrication hole diameter	3 mm
e - Inlet diameter of roller or washer	23 mm
R - Track roller radius	500 mm
Maximum tightening torque	20 N-m
Bearing with/without cage	Avec
Radial clearance class	CN
Precision class	P0
Mass	0,087 kg

PRODUCT PERFORMANCE	
Cr - Dynamic load rating	7850000 mN
C0r - Static load rating	9650000 mN
Track load capacity spherical outer ring	2620000 mN
N lim - Grease lubrication limit speed	60000 °/s
N lim - Oil lubrication limit speed	78000 °/s
Tmin - Min operating temperature	253,15 °K
Tmax - Max operating temperature	393,15 °K

