

## PRECISION STOPWATCH

### USERS' INSTRUCTION

Thank you for your purchase of this delicate stopwatch. The utmost care has gone into the design and manufacture. Please read the manual carefully and keep it for further reference.

#### FEATURES

- Display time, month, date, day of the week
- Daily alarm
- Temperature
- Year of calendar range : 2000-2050
- 199 laps/splits times
- 60 laps/splits memory records
- 10 hours countdown time
- Water resistant

#### PRODUCT DESCRIPTIONS AND FUNCTION KEYS



##### 1. RECALL key:

- In normal time, alarm time and countdown mode, press and hold it for 2 seconds to enter setting mode.
- In setting mode, press it to save and exit the setting.
- In lap/split mode, press it to check the records.

##### 2. SPLIT/RESET key:

- In normal mode, press it to display temperature for 2 minutes.
- In lap/split mode, press it to reset the value.
- In normal time, alarm time and countdown setting mode, press it to step the setting items.

##### 3. LIGHT key:

- Press to turn on the backlight for 7 seconds.

##### 4. MODE key:

- When displaying temperature, press it to switch to Month/Date and Day of the week.
- Press it to switch between normal time mode, lap mode, split mode, countdown mode and alarm mode.
- In setting mode, press it to save and exit setting.

##### 5. START/STOP key:

- When displaying temperature, press it to switch between Celsius and Fahrenheit.
- In normal mode, press and hold it for 2 seconds to turn on/off the key tone.
- In alarm mode, press it to turn on/off the alarm function.
- In lap/split/countdown mode, press it to start or stop counting.
- In setting mode, press it to increase the setting value. Press it without releasing to speed up setting.

#### DISPLAY SYMBOLS


##### Normal Time Mode

1. Month
2. Date
3. Key tone icon
4. Day of the week
5. Time



##### Temperature Display

1. Temperature



1

#### Alarm Time Mode

1. Normal time
2. Alarm time
3. Alarm icon
4. Alarm mode



#### Lap Mode

1. Lap number
2. Stopwatch
3. Current lap time



#### Split Mode

1. Split number
2. Stopwatch
3. Current split time



#### Countdown Mode


1. Countdown circle times
2. Countdown timer
3. Countdown time



#### LAP TIME MEASUREMENT

Through this function, you can know the time spent in every lap. For example, if you want to measure 3-lap time, do the following:

1. In normal mode, press **MODE** key to enter lap mode.
2. Press **START/STOP** key to start to measure the lap time.
3. Press **SPLIT/RESET** key for 3 times to record the time of lap 1, lap 2 and lap 3.
4. Press **START/STOP** key to save the measurement data.
5. Press **MODE** key to exit the lap time measurement mode.



##### Note:


The following picture shows the way of lap time measurement.



#### SPLIT TIME MEASUREMENT

Through this function, you can know the whole split time from the beginning. For example, if you want to measure 3-split time, do the following:

1. In normal mode, press **MODE** key twice to enter split mode. Press **SPLIT/RESET** key to clear the record.
2. Press **START/STOP** key to start to measure the split time.
3. Press the **SPLIT/RESET** key for 3 times to record the time of split 1, split 2 and split 3.
4. Press **START/STOP** key to save the measurement data.
5. Press **MODE** key to exit the split time measurement mode.



2

**Note:**

The following picture shows the way of split time measurement.



**RECALLING THE LAP/SPLIT RECORDS**

1. Measure the lap/split time as described in the previous sections.
2. Press **RECALL** key to enter recall mode, with the icon "SPLIT RECALL" displaying on the LCD.
3. Press **SPLIT/RESET** or **START/STOP** key to check the time records upwards or downwards.
4. Press **MODE / RECALL** key to return to the lap/split mode.




**Note:**

1. The sports timer can display up to 199-lap/split time records, but only memory the first 60 records.
2. The lap and split time records will be displayed together when you recall the lap or split records.

**COUNTDOWN TIME SETTING**

1. In normal mode, press **MODE** key thrice to enter the countdown mode.
2. Press **RECALL** key for 2 seconds until the Hour digit flashes.
3. Press **START/STOP** key to increase the value of the flashing digit.
4. Press **SLPIT/RESET** key to proceed to the next setting. Setting sequence will be: Hour>Minute>Second.
5. Press **RECALL** or **MODE** key to save and exit the setting mode, or let it exit automatically 60 seconds later without pressing any key.



**Note:**

1. The maximum time you set can be 9:59'59"00.
2. After the setting, press **START/STOP** key to start or stop the countdown. It can be operated for 199 times and the countdown cycle times will be displayed on the LCD.
3. The default countdown time is 0:00'00"00 (10 hours). Without setting the countdown time, the countdown timer can also be operated by pressing **START/STOP** key.


**TIME AND CALENDAR SETTING**

1. In normal mode, press and hold **RECALL** key for 2 seconds until the Second digit flashes.
2. Press **START/STOP** key to change the value of the flashing digit.
3. Press **SPLIT/RESET** key until the Minute digit flashes. Press **START/STOP** key to set its value.

4. Repeat above 3 in this order:

Second>Minute>Hour>12/24Hr>Month>Date>Year.

5. Press **MODE** key to save and exit the setting, or let it exit automatically 60 seconds later without pressing any key.



**Note:**

For second setting, press **START/STOP** key to change the value to 00; while for the latter setting items, press **START/SROP** key to increase the values.

**ALARM TIME SETTING**

1. In normal mode, press **MODE** key four times to enter the alarm time mode.
2. Press and hold **RECALL** key for 2 seconds until the Hour digit flashes.
3. Press **START/STOP** key to increase the value of hour.
4. Press **SPLIT/RESET** key to proceed to Minute setting; press **START/STOP** key to increase its value.
5. Press **MODE** key to save and exit setting mode, or let it exit automatically 60 seconds later without pressing any key.



**Note:**

1. The alarm will be automatically turned on after you set the alarm time.
2. Press any key to stop the ringing bell. The sound duration is 60 seconds.

**KEY TONE SETTING**

In normal mode, press and hold **START/STOP** key for 2 seconds to turn on the key tone with the icon "🎵" displaying on the LCD. Press and hold **START/STOP** key for 2 seconds again to turn off the key tone. The icon disappears.

**BATTERY REPLACEMENT**

If there is no display on the LCD or if the display becomes dim, remove the screws in the back of the unit and replace with one new CR2032 battery according to the polarity mark.

**Note:**

Attention! Please dispose of the used unit or batteries in an ecologically safe manner.

