

## Features

- Rotation Swivel
- Nylon
- Fixed Plate
- Corrosion Resistant
- Impact Resistant

## RS PRO Castor Wheels

RS Stock No.: 0631181



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

## Product Description








Castors in zinc-chromium plated pressed steel, turning on double rim of balls. Nylon wheel. Recommended use for office furnitures, metal furnishing, electrical household, etc.

## General Specifications

Rotation	Swivel
Weight Class	
Load Capacity (Kg)	40
Load Capacity / 4pcs (Kg)	120
Tyre Material	Nylon
Hub Material	Nylon
Bracket Material	Pressed Steel
Includes Brake	No
Features	Corrosion Resistant, Impact Resistant
Applications	

## Operation Environment Specifications

Operating Temperature (Celsius)	
---------------------------------	--

						
50x23	29	40x40	42x42	6,5x10	75	40

## Mechanical Specifications

<b>Mounting Type</b>	Single Bolt
<b>Wheel Diameter (mm)</b>	50
<b>Wheel / Tread Width (mm)</b>	23
<b>Overall Height (mm)</b>	75
<b>Number of Fixing Holes</b>	4
<b>Fixing Hole Size (mm)</b>	6.5x10
<b>Hub Bearing Type</b>	Plain Bore
<b>Thread Size (M)</b>	
<b>Stem Height (mm)</b>	
<b>Stem Diameter (mm)</b>	
<b>Hardness of Wheel (Shore A)</b>	
<b>Levelling Extent (mm)</b>	
<b>Offset (mm)</b>	
<b>Castor Weight (Kg)</b>	0.232

## Fixing Centres Specifications

<b>Fixing Centres (mm)</b>	40x40
<b>Fixing Centres Length (mm)</b>	40
<b>Fixing Centres Width (mm)</b>	40

## Fixing Plate Specifications

<b>Fixing Plate Dimensions (mm)</b>	42x42
<b>Fixing Plate Length (mm)</b>	42
<b>Fixing Plate Width (mm)</b>	42