

# Rittal – The System.

Faster – better – everywhere.

## ► Vario rack-mounted fans for 482.6 mm (19") Air throughput 320 – 480m<sup>3</sup>/h – SK 3352.500

Date : Apr 26, 2021

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# Vario rack-mounted fans for 482.6 mm (19") Air throughput 320 – 480m³/h – SK 3352.500

created: 26.04.2021 build on [www.rittal.com/uk-en](http://www.rittal.com/uk-en)



Product description	
Description:	Rack-mounted fan for direct installation in the 482.6 mm (19") level. Installation allows air to circulate permanently inside the enclosure, thus preventing the formation of hot spots.
Benefits:	Guide frame ensures easy maintenance and replacement of the fans
Colour:	RAL 7035
Supply includes:	Fully wired unit ready for connection Terminal strip and assembly parts
Note on Model No.:	Extended delivery times.
Product description	
Total cooling output/Number of fan modules:	
Air throughput (unimpeded air flow):	480 m³/h
Rated operating voltage:	115 V - 230 V, 1~, 50 Hz/60 Hz 24 V (DC)
Dimensions:	Width: 482.6 mm Height: 44 mm Depth: 200 mm
Distance between	105 mm

<b>axes of fans:</b>	
<b>Temperature range:</b>	Operation (environment): -10 °C...+55 °C
<b>Rated current max.:</b>	At 50 Hz: 0.85 A At 60 Hz: 0.85 A
<b>Miniature circuit-breaker/fuse:</b>	6 A
<b>Noise level:</b>	At 50 Hz: 51 dB(A)
<b>No. of fans:</b>	3
<b>eCl@ss 8.0/8.1:</b>	27180716
<b>Packs of:</b>	1 pc(s).
<b>Weight/pack:</b>	2.04 kg
<b>EAN:</b>	4028177041660
<b>Customs tariff number:</b>	84145915
<b>ETIM 7.0:</b>	EC000320
<b>ETIM 6.0:</b>	EC000320
<b>eCl@ss 8.0/8.1:</b>	27180716
<b>eCl@ss 6.0/6.1:</b>	27180716
<b>Product description:</b>	SK rack-mounted fan, for 482.6 mm (19"), 480 m³/h, 115-230 V, 1~, 50/60 Hz, 24 V (DC), WHD: 482.6 x 44 x 200 mm
<b>Approvals</b>	
<b>Approvals:</b>	Approval overview UR + C-UR
<b>Certificates:</b>	EAC
<b>Declarations:</b>	Declaration of conformity