






Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet. Zuwiderhandlungen verpflichten zu Schadenersatz. Alle Rechte für den Fall der Patent-, Gebrauchsmuster- oder Designeintragung vorbehalten.
Bauartbedingtes Spiel ist in den Toleranzangaben nicht berücksichtigt.

Transfer or duplication of this document as well as the utilisation or communication of its content are not permitted unless express consent is granted. Violations give rise to claims for damages. All rights reserved in case of patent, utility model or design patent registrations.
Tolerance specifications do not include clearances inherent in the design.



- EN ISO 291 23/50

 DIN A4		document-no. / ri 01363232 / 01		article-no. 1232243		scale 1:10		- Simplified representation - Document excluded from change process - Linear dimensions [mm]
		date 08.08.2024	document-type TECDOC 2D_Productdrawing					
		description CHARX PS-M2/3AC/1000DC/30KW						
page 1		of 1						