

HandiMark / TLS2200 : Technical specifications of the HandiMark / TLS2200 Quick Charger's power supply?

Article ID: 5072 Version: Last Modified: 1/31/2012 5:55:23 PM Usage: 166

Input: 100-240V~50/60Hz
37-48VA
0.6A

Output: 24V
1.0A
Center Positive

Attached is a picture of the power supply that comes with the Quick Charger.

*Note - The standard battery charger that comes with both the HandiMark and the TLS2200 printers has a lower output voltage than that of the power supply (A/C adapter) made for the Quick Charger. The standard battery charger is an A/C adapter that plugs directly into a HandiMark / TLS2200 battery and is not designed to power the Quick Charger.

© Copyright 2012 Brady Worldwide Inc. All Rights Reserved



PLUG-IN BATTERY CHARGER

- Accessory Type: Printer Battery Charger
- For Use With: Brady TLS 2200 Thermal Label Printer
- Battery Charger Type: Plug In
- Supply Voltage: 120V
- Charge Current Max: 183mA
- Frequency: 60Hz

**United Kingdom, Ireland,
South Africa**

Power cord specifications

plug:	BS 1363A
connector:	IEC 320
conductor size:	3 x 1.00 mm ²
description:	H05VVF3G1.0
typ. stranding:	32/0.2 mm
current rating:	10A
voltage rating:	250 VAC
maximum length:	less than 3 meters

