



USB AポートをLANポートに変換し、有線で安定した高速ネットワーク接続を実現。ドライバー不要で簡単接続。1m。

KB-SL6ALAN01BK

USB A LAN変換ケーブル（Gigabit対応・1m）

JANコード 4969887774601



仕様

形状タイプ	極細タイプ
カテゴリ	CAT6
規格名	1000BASE-TX
対応カテゴリ・規格	カテゴリ6（1000BASE-TX）、カテゴリ5e（1000BASE-T）、カテゴリ5（100BASE-TX）、カテゴリ3（10BASE-T）適合
通信速度	1Gbps
周波数特性	250MHz
ケーブル長	1m
カラー	ブラック
ケーブル直径	4.2mm
結線仕様	ストレート結線
ケーブル構造	STP
十字介在	無

ケーブル導体	32AWG
ケーブル導体構造	より線
PoE	非対応
被覆材質	PVC
コネクタ形状	USB A - RJ-45
スリムコネクタ	無
ツメ折れ防止コネクタ	無
ツメ折れ防止カバー	有
動作湿度	10～85%
検査	100%導通検査

特長

USB AポートをLANポート（RJ-45）に変換し、有線ネットワークに直接接続が可能です。

LANポート非搭載のパソコンでも、ケーブル1本でスムーズに有線接続できます。

有線接続により、Wi-Fiよりも安定した高速通信を実現します。

最大1Gbps（1000Mbps）の高速データ通信に対応します。

MACアドレスのパススルー機能に対応で、ネットワークのセキュリティ管理にも最適です。

※パソコンがMACアドレスのパススルー機能に対応している必要があります。

ツメ折れ防止カバー付きLANコネクタ採用で、耐久性を向上しています。

※使用中、USB Aコネクタ部が熱を持つ場合がありますが、仕様の範囲内で問題ありません。

対応情報

対応機種	Windows搭載（DOS/V）パソコン Apple Macシリーズ Chrome OS搭載パソコン など ※USBポート（USB-A メス）を持ち、パソコン本体メーカーがUSBポートの動作を保証している機種。 ※USB5Gbps（USB3.2 Gen1）の環境で動作させるためにはパソコン本体にUSB5Gbps(USB3.2 Gen1)ポートが必要です。 ※ギガビット(1000BASE-T)通信で動作させるためにはパソコン本体のUSB3.2 Gen1ポートへの接続が必要。 ※USB2.0/1.1ポートへの接続時は100BASE-TX/10BASE-Tの通信速度になります。
------	---

**Converts a USB A port into a LAN port, providing a stable, high-speed wired network connection. Easy connection with no drivers required. 1m.
KB-SL6ALAN01BK**

Specification

- Shape Type : Ultra-thin type
- category : CAT6
- Standard name : 1000BASE-TX
- Supported categories and standards : Category 6 (1000BASE-TX), Category 5e (1000BASE-T), Category 5 (100BASE-TX), Category 3 (10BASE-T) compatible
- communication speed : 1Gbps
- Frequency response : 250MHz
- Cable length : 1m
- Color : black
- Cable diameter : 4.2mm
- Wiring specifications : Straight connection
- Cable Structure : STP
- Cross intervention : None
- Cable conductor : 32AWG
- Cable conductor structure : Stranded wire
- PoE : Not supported
- Coating Material : PVC
- Connector Shape : USB A to RJ-45
- Slim Connector : None
- Anti-break connector : None
- Claw breakage prevention cover : Yes
- Operating Humidity : 10–85%
- Inspection : 100% continuity test

Features

- Converts the USB A port into a LAN port (RJ-45), allowing direct connection to a wired network.
- Even if your computer does not have a LAN port, you can easily connect via a wired connection with just one cable.
- A wired connection provides more stable and faster communication than Wi-Fi.
- Supports high-speed data communication of up to 1Gbps (1000Mbps).
- Supports MAC address pass-through, making it ideal for network security management.
*The MAC address pass-through function must be supported by your computer.
- The LAN connector has a cover to prevent the tabs from breaking, improving durability.
*The USB A connector may become hot during use, but this is within the specifications and does not cause any problems.