

Product data sheet

179 N W-7/230

EAN-No. 4000896219605



230-pieces · 7 Drawers total



- More storage space than preceding model
- 6 flat drawers, loading capacity 25 kg, 81 mm high
1 high heavy-duty drawer, loading capacity 40 kg, 166 mm high
- Complete with 230-piece tool assortment in Safety-Insert-System soft foam insert
- 30 mm wood multiplex birch work surface, oiled, replaceable
- Including nine-fold adjustable intermediary tray and fixed mounted door
- Cable aperture on rear panel allows, for example battery-powered devices to be charged when the door is locked
- Complete welded construction of the entire body for tough daily workshop use
- Additional square perforation for tool holder, e.g. HAZET 112-230
- Optimised, yielding edge protection on all four corners with real impact protection thanks to internal damping concept
- Flexible vice assembly (front, right, left) e.g. HAZET 2175N as per drilling templates
- **Chassis:**
 - Large wheels with high loading capacity (Ø 125 mm) with precision ball-bearing and dual ball race in the swivel bearing, easy manoeuvrability even under high dynamic load
 - 2 swivel castors with dual brake:
 - Braked castors prevent rolling away
 - Braked swivel bearings prevent the swivel castors from turning, e.g. on inclined surfaces
 - Protective ring prevents dirt and threads from getting in
 - Elastic castors enable smooth movement
- **Locking concept:**
 - Mutual drawer locking for minimum tilting risk
 - Lock located in the centre (central locking and cylinder lock) closes the door and drawers at the same time
 - Only one key for locking the door and drawers at the same time (Included in delivery: 2 keys)
 - 180° rotation, prevents the key from breaking off
 - 100 % sliding-out with ball-bearing telescopic rails – self-closing
 - Lockable storage compartment with 2 storage surfaces
- 2 storage spaces in the storage compartment, top: 15 kg / bottom: 35 kg
- Total loading capacity (dynamic): 750 kg
- Loading capacity (static): 1000 kg
- Worktop: Wood multiplex birch, replaceable
- Colour: HAZET blue
- Tool trolley Made in Germany
- Dimensions: 1150 mm x 600 mm x 964 mm
- Net weight: 120 kg
- Drawers, flat: 6 x 81 x 522 x 398 mm
- Drawers, high: 1 x 166 x 522 x 398 mm
- (Drawer) size for plastic drawer insert: 3/3+
- Worktop: Wood multiplex birch, replaceable

EAN-No. 4000896**219605**

- Number of fixed castors: 2 (Ø 125 mm)
- Number of swivel castors: 2 (Ø 125 mm)
- Number of tools: 230

Order Number

179 NW-7/230



179NW-7



163-372/25 • ●



612N • ●
10 x 11



666-5

730

730-3 • 730-6

746-1

748B

748B-3 • 748B-4 • 748B-5 • 748B-6 • 748B-8

824 • —

0.5 x 23

1952-40

1976-2

2140-40

2147MS

2152N/3



2154N-5



2157-1



4968-2



163-513/122N

















811BML • 

850 •  • 

5.5 • 6 • 7 • 8 • 9 • 10 • 11 • 12 • 13

850E •  • 

E5 • E6 • E7 • E8 • E10



863HP • 



867-2 •  • 



868 •  • 



869 •  • 

880 •  • 

10 • 11 • 12 • 13 • 14 • 15 • 16 • 17 • 18 • 19 • 21 • 22



8816HP • 



8820 •  • 

8821 •  • 

8821-3 • 8821-6 • 8821-10

8858-2 •  • 

900 •  • 

10 • 11 • 12 • 13 • 14 • 15 • 16 • 17 • 18 • 19 • 20 • 21 • 22 • 23 • 24 • 26 • 27 • 28 • 30 • 32

900E •  • 

E10 • E12 • E14 • E16 • E18 • E20



915 • 



916HP • 

917-5 •  • 

918-10 •  • 



920 •  • 

958-2 •  • 

1058-2 •  • 

2204N •  • 

2 • 2.5 • 3 • 4 • 5 • 6

2208N •  • 

0.5 x 4 • 0.6 x 4.5 • 0.8 x 5.5 • 1 x 6

2215N •  •  • 

PH1 • PH2 • PH3

2216N •  •  • 

PZ1 • PZ2 • PZ3

2223N •  • 

T6 • T7 • T8 • T9 • T10 • T15 • T20 • T25 • T27 • T30 • T40

2223N •  • 

T10H • T15H • T20H • T25H • T27H • T30H



2239N-6 •  •

Product data sheet

179 N W-7/230

EAN-No. 4000896219605



163-526/41N

•, •, •, •



811 •

0.4 x 2.5 • 0.5 x 3 • 0.8 x 4 •

1 x 5.5 • 1.2 x 6.5



811PH •

PH0 • PH1 • PH2



811T •

T10 • T15 • T20 • T25 •

T27 • T30



811K •

0.6 x 3.5 • 1 x 5.5



811KPH •

PH1 • PH2



811S •

0.8 x 4.5 • 1 x 5.5 • 1.2 x 7



811SPH •

PH1 • PH2 • PH3



2105LG/9H •



2116LG/8H •