



tesa[®] 4961

Product Information



Double-sided tape with paper backing

Product Description

tesa[®] 4961 consists of a natural rubber adhesive and special paper backing. The "hard" adhesive system provides good shear resistance and can also be removed without leaving adhesive residues.

Product Features

- The "hard" adhesive system provides good shear resistance and can also be removed without leaving adhesive residues.

Application Fields

- Splicing of paper and film
- Self-adhesive mounting of sanding discs
- General mounting on smooth surfaces

Technical Information (average values)

The values in this section should be considered representative or typical only and should not be used for specification purposes.

Product Construction

- | | | | |
|--------------------|----------------|-------------------|--------|
| • Backing material | flat paper | • Total thickness | 205 µm |
| • Type of adhesive | natural rubber | • Colour | white |
| • Type of liner | glassine | • Colour of liner | brown |

Properties/Performance Values

- | | | | |
|--------------------------|---------|--|--------------|
| • Elongation at break | 3 % | • Softener resistance | medium |
| • Tensile strength | 90 N/cm | • Static shear resistance at 40°C | very good |
| • Ageing resistance (UV) | medium | • Tack | good, medium |
| • Chemical resistance | medium | • Temperature resistance long term duration | 40 °C |
| • Humidity resistance | medium | • Temperature resistance short term duration | 110 °C |



tesa[®] 4961

Product Information

Adhesion to Values

• ABS (initial)	6 N/cm	• PET (after 14 days)	5.8 N/cm
• ABS (after 14 days)	6.6 N/cm	• PP (initial)	5.4 N/cm
• Aluminium (initial)	6.1 N/cm	• PP (after 14 days)	6.7 N/cm
• Aluminium (after 14 days)	6.6 N/cm	• PS (initial)	7 N/cm
• PC (initial)	7.3 N/cm	• PS (after 14 days)	7.7 N/cm
• PC (after 14 days)	7.5 N/cm	• PVC (initial)	6.2 N/cm
• PE (initial)	3.9 N/cm	• PVC (after 14 days)	6.3 N/cm
• PE (after 14 days)	4.1 N/cm	• Steel (initial)	7.8 N/cm
• PET (initial)	5.7 N/cm	• Steel (after 14 days)	8 N/cm

Disclaimer

tesa[®] products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa[®] product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.



For latest information on this product please visit <http://l.tesa.com/?ip=04961>