

Product selected: DE ECO 118MM 120W 240V R7S 2000H

Product Attributes	
Item description	DE ECO 118MM 120W 240V R7S 2000H
Ordering Code	0021714
EAN Code	5410288217147
Bulb shape	Linear
Bulb finish / Light colour	Clear
Nominal wattage (W)	120
Rated wattage at 50 Hz (W)	120
Equivalent Inc. Lamp power (W)	-
Lamp power factor	1
Cap	R7s
Dimmable	Yes
Nominal Voltage (V)	240
Nominal average life (h)	2000
Rated lamp life (h)	2000
Bulb finish / Light colour	Clear
Colour temperature (K)	2950
Nominal luminous flux at 25°C (lm)	2250
Rated luminous flux at 25°C (lm)	2250
Lumen maintenance at end nom. Life (%)	80
Diameter D [mm]	12
Mercury content per lamp [mg]	0,0
Starting time (sec)	0.01
Warm-up time to 60% of full light	Instant full light
No. Of switching cycles before premature failures	> 8000 x
Optimal operating conditions	25°C
Packing Quantity	100

## Product Image



## Cap (image)

