

Rittal – The System.

Faster – better – everywhere.



SZ 2411.651

Cable gland, polyamide

Stand: 1/2/2023 (Quelle: rittal.com/in-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 2411.651 - Cable gland, polyamide

Integrated clamping membranes ensure reliable tightening and strain relief to protect the cables.

Eigenschaften

Model No.	SZ 2411.651
Benefits	Because the gland and lock nut are sold together in a single pack, this saves additional ordering and storage. Clamping membranes for even tightening and strain relief to protect the cables
Material	Polyamide 6 Seal: CR/NBR
Colour	RAL 7035
IP protection category to IEC 60529	IP 68 (5 bar, 30 min)
Dimensions	Height: 47.5 mm
Thread	M40 x 1.5
Thread length	10 mm
Min. cable diameter	19 mm
Max. cable diameter	28 mm
Operating temperature range	-30 °C...100 °C
torque	12 Nm
Width across flats	46 mm
Dimensions	Thread: M40 x 1.5 Thread length: 10 mm
Type rating to UL 50E	Type 4X
Packs of	5 pc(s).
Weight/pack	0.47 kg
Copper weight (kg per piece)	0

Eigenschaften

Customs tariff number	39269097
EAN	4028177809956
ETIM 7.0	EC000441
ECLASS 8.0	27149109

Approbationen

Approbationen	CSA + CSAus GOST UL + C-UL (listed) VDE
Erklärungen	Declaration of conformity
